

# Filling Valves



**JST ENGINEERING CO.,LTD.**  
78/6 MOO 7 KINGKAEW RD., RACHATEWA.  
BANGPLEE, SAMUTPRAKARN 10540 THAILAND.



ศูนย์รวม 081-684-0565  
ลูกค้าไทย 098-825-8600  
ลูกค้าต่างประเทศ 092-247-6565












Facebook Page

+66 (0) 2738 5050-4 URL: www.jst.co.th  
+66 (0) 2738 5055 LINE ID: atithep.jst  
info@jst.co.th www.facebook.com/LWCompressor



Accessories

	Order number	P max / Application	Mount	Repair kit/ special tools/ silencer
	<b>Cross design filling valve without pressure gauge</b>			
	Yoke: 003686 DIN 200: 003684 DIN 300: 003685	350 bar Filling valve with separate vent screw	Filling valve without pressure gauge for hose with swivel connection. (Standard connection 8S)	Repair kit: 002294
	<b>Cross design filling valve with pressure gauge</b>			
	Yoke: 003689 DIN 200: 003687 DIN 300: 003688	350 bar Filling valve with separate vent screw	Filling valve with pressure gauge for hose with swivel connection. (Standard connection 8S)	Repair kit: 002294
	<b>Overflow valve with venting</b>			
	DIN 200: 009327 DIN 300: 009328	350 bar Overflow valve with pressure gauge and with venting for connection of two cylinders	Connection thread 009327: 2 x DIN 200 (5/8") Connection thread 009328: 2 x DIN 300 (5/8")	Repair kit: 002294
	<b>Hand wheel valve without venting</b>			
	001477	350 bar Standard 2/1 way valve, G $\frac{1}{2}$ " inlet and outlet for opening closing lines such as storage cylinders	For panels with diameter of bore 33 mm	Lower seat: 000571 Upper valve stem and bearing: 000573
	<b>Hand wheel valve without venting</b>			
	001476	350 bar Standard 2/1 way valve, G $\frac{1}{2}$ " inlet and outlet self venting on the outlet line for filling panels	For panels with diameter of bore 33 mm	Lower seat: 000572 Upper valve stem and bearing: 000574 Silencer kit: 002896
	<b>Lever filling valve, self venting</b>			
	200 bar: 002449 300 bar: 002450	350 bar Standard 2/1 way valve, G $\frac{1}{2}$ " inlet and M16 x 1.5 mm outlet self venting on the outlet line for filling panels	Panel mounting inside a 90° profile secured by 4 screws, vents inside the panel	Repair kit small: 002451 Repair kit large: 002452 Werkzeugsatz: 002453 Silencer kit: 000580
	<b>Lever filling valve, self venting (by 2005)</b>			
	No longer available	350 bar Standard 2/1 way valve, G $\frac{1}{2}$ " inlet and outlet self venting on the outlet line for filling panels	Panel mounting inside a 90° profile secured by 4 screws, vents inside the panel. (limited availability)	Repair kit: 000576 Tool kit: 000575 Silencer kit: 000580
	<b>Lever filling valve, self venting (by 2005)</b>			
	No longer available	350 bar Standard 2/1 way valve, G $\frac{1}{2}$ " inlet and M16 x 1,5mm male outlet, self venting on the outlet line for filling panels with hoses	Panel mounting with $\varnothing$ 23 mm hole silencer integrated in the vent	Repair kit: 000576 Tool kit: 000575
	<b>Lever filling valve, self venting</b>			
	No longer available	350 bar Standard 2/1 way valve, G $\frac{1}{2}$ " inlet and M16 x 1.5 mm outlet self venting on the outlet line for filling	Vertical panel mounting with U Clamp	U Clamp: 001826 Repair kit small: 001834 Repair kit large: 001836